

Product data sheet

Specifications

Actassi - vertical power distribution rail - 12 sockets+circuit breaker UTE



NSYAPUF12CB

Main

Range	Actassi
Product Or Component Type	Power distribution rail
Device Application	Multi-purpose
Outlet Standard Description	Pin earth
Accessory / Separate Part Category	Current distribution accessory
Outlet Poles Configuration	2P + E with shutters
Quantity Per Set	Set of 1
Colour	Aluminium

Complementary

Device Composition	1 power rail fixing elements
Ground Lug Position	35° ground lug
Socket Number	12
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	230 V AC
Protection Type	Overvoltage protection C60N 16 A curve C
Mounting Support	Upright
Fixing Mode	By brackets
Material	Polyamide 6 with 30 % fibre glass
Surface Finish	Anodized
Electrical Connection	3 m power cord 3 x 1.5 mm² H05VV-F3G1.5
Width	1232 mm
Depth	76 mm

Environment

Fire Resistance	850 °C
Quality Labels	UTE
Standards	NBN C 61-112-1 NFC 61-314 IEC 60884

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	10.5 cm
Package 1 Length	121.8 cm
Package 1 Weight	2.446 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	80
Package 2 Height	150.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	209.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations