

# Product data sheet

Specifications



## Airing grille cut-out diameter 19mm IP45

NSYCAG19LP

### Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS
Product Or Component Type	Plastic ventilation louver
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Mounting Position	Vertical
Fixing Mode	By screws
Device Composition	2 plastic louver

### Complementary

Material	Polyamide 6
Colour	Grey (RAL 7035)
Cut-Out Dimensions	19 mm
Height	30 mm external:
Width	23.5 mm external:
Depth	22 mm external:
Ip Degree Of Protection	IP45

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	11.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	7.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	300
Package 2 Height	19.0 cm
Package 2 Width	24.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	35.0 cm
Package 2 Weight	2.1 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations