

# Product data sheet

Specifications



## Airing grille cut-out diameter 38mm IP45

NSYCAG38LP

### Main

|                                       |   |
|---------------------------------------|---|
| Range                                 | ClimaSys  |
| Product                               | ClimaSys CA   |
| Range Compatibility                   | Thalassa Thalassa PLS<br>Thalassa Thalassa PLM<br>Thalassa Thalassa TBS |
| Product Or Component Type             | Plastic ventilation louver  |
| Accessory / Separate Part Category    | Thermal management accessory  |
| Accessory / Separate Part Destination | ClimaSys ventilation system   |
| Fixing Mode                           | By screws   |
| Device Composition                    | 2 plastic louver  |

### Complementary

|                         |                 |
|-------------------------|-----------------|
| Material                | Polyamide 6     |
| Colour                  | Grey (RAL 7032) |
| Cut-Out Dimensions      | 38 mm           |
| Height                  | 63 mm external: |
| Width                   | 63 mm external: |
| Depth                   | 15 mm thread:   |
| Ip Degree Of Protection | IP45            |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 3.5 cm  |
| Package 1 Width              | 10.0 cm |
| Package 1 Length             | 11.0 cm |
| Package 1 Weight             | 58.0 g  |
| Unit Type Of Package 2       | CAR     |
| Number Of Units In Package 2 | 200     |
| Package 2 Height             | 40.0 cm |
| Package 2 Width              | 40.0 cm |
| Package 2 Length             | 60.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Package 2 Weight             | 12.282 kg |
| Unit Type Of Package 3       | P12       |
| Number Of Units In Package 3 | 1600      |
| Package 3 Height             | 120 cm    |
| Package 3 Width              | 80 cm     |
| Package 3 Length             | 97 cm     |
| Package 3 Weight             | 111 kg    |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |