

Product data sheet

Characteristics

NSYCCOTH230VID

Climasys CC - Electronical thermostat 200..240V
- range of temperature -40...80°C



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Electronical thermostat
Temperature setting range	-40...80 °C
Display type	OLED screen
Information displayed	Temperature in °F Temperature in °C

Complementary

Input voltage	200...240 V AC
Sensor type	Optional NTC external sensor
Maximum switching capacity	4 A 230 V AC
Electrical connection	10 terminals 2.5 mm ²
Mounting mode	Clipped By screws
Height	External : 85 mm
Width	External : 56 mm
Depth	External : 44 mm
Mounting location	Cross rails Spacial upright On mounting plate 35 mm DIN rail
Ambient air temperature for operation	-40...80 °C
Hysteresis	2 K programmed value
Number of outputs	2 output(s) ventilation/heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
