



Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-water exchanger
Mounting type	Sides of enclosure
Cooling power	1750 W

Complementary

Pressure	5 bar for water
Pressure drop	0.1 bar
Water flow	Internal circuit : 150 l/h
Flow rate	External circuit : 570 m ³ /h
Control type	Thermostat
Temperature setting range	20...46 °C
Ambient air temperature for operation	Outside the enclosure : 1...70 °C Inside the enclosure : 20...60 °C
Controlled fluid	Water
Fluid connection type	G 1/2 (female)
Input voltage	230 V 50/60 Hz
[In] rated current	0.36 A
Power consumption in W	75 W
Height	External : 901 mm
Width	External : 398 mm
Depth	External : 137 mm
Product weight	18 kg
Noise level	58 dB
Protection type	Thermal protection : T 2 A
Material	Steel
Colour	Grey RAL 7035

Environment

IP degree of protection	IP55 on the external circuit conforming to IEC 60529
-------------------------	--

IP55 on the internal circuit conforming to IEC 60529

Product certifications	UL
Standards	DIN 3168

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
