



### Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-water exchanger
Mounting type	Sides of enclosure
Cooling power	2500 W

### Complementary

Pressure	5 bar for water
Pressure drop	0.3 bar
Water flow	Internal circuit : 500 l/h
Flow rate	External circuit : 860 m <sup>3</sup> /h
Control type	Thermostat
Temperature setting range	20...46 °C
Ambient air temperature for operation	Outside the enclosure : 1...70 °C Inside the enclosure : 20...60 °C
Controlled fluid	Water
Fluid connection type	G 1/2 (female)
Input voltage	230 V 50/60 Hz
[In] rated current	0.33 A
Power consumption in W	80 W
Height	External : 901 mm
Width	External : 398 mm
Depth	External : 137 mm
Product weight	19 kg
Noise level	58 dB
Protection type	Thermal protection : T 2 A
Material	Steel
Colour	Grey RAL 7035

### Environment

IP degree of protection	IP55 on the external circuit conforming to IEC 60529
-------------------------	--

IP55 on the internal circuit conforming to IEC 60529

---

Product certifications

UL

---

Standards

DIN 3168

---

## Offer Sustainability

---

RoHS (date code: YYWW)

Compliant - since 0940 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

---

REACH

Reference not containing SVHC above the threshold

[Reference not containing SVHC above the threshold](#)

---