



### Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-water exchanger
Mounting type	Sides of enclosure
Cooling power	15000 W

### Complementary

Pressure	8 bar for water
Pressure drop	4.8 bar
Water flow	Internal circuit : 2000 l/h
Flow rate	External circuit : 2900 m3/h
Control type	Thermostat
Temperature setting range	20...46 °C
Ambient air temperature for operation	Outside the enclosure : 1...70 °C Inside the enclosure : 20...60 °C
Controlled fluid	Water
Fluid connection type	G 3/4 (female)
Input voltage	230 V 50/60 Hz
[In] rated current	1.4 A
Power consumption in W	320 W
Height	External : 1932 mm
Width	External : 797 mm
Depth	External : 206 mm
Product weight	92 kg
Noise level	72 dB conforming to EN/ISO 3746
Protection type	Thermal protection : T 4 A
Material	Stainless steel
Colour	Grey RAL 7035

### Environment

IP degree of protection	IP55 on the external circuit conforming to IEC 60529
-------------------------	--

IP55 on the internal circuit conforming to IEC 60529

Product certifications	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2006/42/EC - machinery
Standards	EN/ISO 12100 EN 60204-1 EN 60335-1 EN 60335-2-40

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>