



### Main

Range	Spacial
Product or component type	Cable gland
Accessory / separate part category	Cable management accessory
Application	ATEX certified application
Range compatibility	Spacial CRN Spacial S3D Spacial S3X
Mounting location	Enclosure top Enclosure bottom
Cable entry	Cable gland M12
Device composition	1 cable gland 1 lock nut 1 seal
Quantity per set	Set of 10
Material	Nickel plated brass for body CR (chloroprene) for seal

### Complementary

Colour	Grey
Surface finish	Chromium plated
Fixing mode	By nut Screwed
Height	39.5 mm
Product weight	0.051 kg

### Environment

Product certifications	DNV-GL UL ATEX EAC INMETRO
Marking	Ex d IIC Gb Ex II 2GD Ex tb IIIC Db Ex e IIC Gb

---

Ambient air temperature for operation	-40...80 °C
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

---