

Product data sheet

Specifications



Set of cable gland + nut stainless steel M12 AISI304L, IP68, UL approved

NSYCGX12

Main

Range	Spacial
Product Or Component Type	Cable gland
Accessory / Separate Part Category	Cable management accessory
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Mounting Location	Enclosure top Enclosure bottom
Cable Entry	Cable gland M12
Device Composition	1 cable gland 1 lock nut 1 seal
Quantity Per Set	Set of 5
Material	Body: stainless steel AISI 304L

Complementary

Colour	Grey
Fixing Mode	Screwed By nut
Height	28 mm
Net Weight	0.011 kg

Environment

Product Certifications	VDE
Flame Retardance	V2 conforming to UL 94
Ambient Air Temperature For Operation	-20...100 °C permanent -40...150 °C intermittent
Ip Degree Of Protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	2 cm
Package 1 Length	3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	14 g
------------------	------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)