

# Product data sheet

Specifications



## Set of cable gland + nut stainless steel M25 AISI304L, IP68, UL approved

NSYCGX25

### Main

Range	Spacial
Product Or Component Type	Cable gland
Accessory / Separate Part Category	Cable management accessory
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Mounting Location	Enclosure top Enclosure bottom
Cable Entry	Cable gland M25
Device Composition	1 cable gland 1 lock nut 1 seal
Quantity Per Set	Set of 4
Material	Seal: CR (chloroprene) Body: stainless steel AISI 304L

### Complementary

Colour	Grey
Fixing Mode	Screwed By nut
Height	35.5 mm
Net Weight	0.025 kg

### Environment

Product Certifications	VDE
Flame Retardance	V2 conforming to UL 94
Ambient Air Temperature For Operation	-20...100 °C permanent -40...150 °C intermittent
Ip Degree Of Protection	IP68 conforming to IEC 60529 5 bar, 30 min

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	3 cm
Package 1 Length	3.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Package 1 Weight	49 g
------------------	------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)