

NSYCMUIA80

Articulated tube joint, square 80 mm, cast steel
RAL 7040. For S3CM HMI encl.



Main

Range	Spacial
Accessory / separate part category	Cable management accessory
Product or component type	Tube adaptor
Application	Multi-purpose
Mounting location	Between 2 horizontal tubes
Mounting support	For 80 mm square tube Option of passing cables through the inside
Range compatibility	Spacial S3CM
Device composition	fixing elements 1 linking and rotating bracket 1 bellow
Quantity per set	Set of 1

Complementary

Material	Moulded steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By fixing element - screw type M12 - horizontal tube location
Operating angle	170 °
Permanent permissible load	10 kg
Height	190 mm
Width	190 mm
Depth	320 mm
Net weight	10.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------