



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	10 W
Input voltage	12...24 V DC
Electrical connection	Cable 2 x 0.75 mm ² length: 300 mm

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	VDE UL
Material	Extruded aluminium for body
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------