



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	20 W
Input voltage	12...24 V DC
Electrical connection	Cable 2 x 0.75 mm <sup>2</sup> length: 300 mm

### Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	UL VDE
Material	Extruded aluminium for body
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By clips
Mounting support	35 mm DIN rail

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------