

# Product data sheet

Specifications



## Climasys Ultra thin resistance heater low starting current 12W 240V 110x140mm

NSYCRS10W240V

### Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	12 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable length: 2 m

### Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-60...70 °C
Temperature Setting Range	-40...70 °C
Material	Silicone rubber
Height	110 mm external:
Width	140 mm external:
Depth	1.6 mm external:
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing Mode	By 4 screws
Mounting Support	Standard mounting plate Adhesive Velcro DIN rail Telequick mounting plate

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	25.5 cm
Package 1 Length	28.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	280.0 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	440
Package 2 Height	172.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	137.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations