


Product data sheet

Specifications



Climasys Ultra thin resistance heater low starting current 195W 240V 400x650mm

NSYCRS200W240V

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	195 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable length: 2 m

Complementary

Operating Position	Horizontal Vertical
Ambient Air Temperature For Operation	-60...70 °C
Temperature Setting Range	-40...70 °C
Material	Silicone rubber
Height	380 mm external:
Width	650 mm external:
Depth	1.6 mm external:
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing Mode	By 4 screws
Mounting Support	Adhesive Velcro Telequick mounting plate Standard mounting plate DIN rail

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	43.0 cm
Package 1 Length	69.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.13 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	150.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	47.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations