



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	25 W
Input voltage	120 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	External: 110 mm
Width	External: 230 mm
Depth	External: 1.6 mm
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing mode	By 4 screws
Mounting support	DIN rail Adhesive Velcro Standard mounting plate Telequick mounting plate

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
