

# Product data sheet

Specifications



## Fontal covers stainless steel for side cooling units 400W

NSYCUSP0085

### Main

|                           |                                  |
|---------------------------|----------------------------------|
| Range Of Product          | ClimaSys                         |
| Product Or Component Type | Cover                            |
| Product Destination       | Side-mounting cooling unit 400 W |
| Offer Type                | Spare part                       |

### Complementary

|                        |                 |
|------------------------|-----------------|
| Material               | Stainless steel |
| Height                 | 460 mm          |
| Width                  | 385 mm          |
| Depth                  | 180 mm          |
| Product Certifications | CE              |
| Quantity Per Set       | 1               |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 53.0 cm |
| Package 1 Width              | 28.2 cm |
| Package 1 Length             | 34.1 cm |
| Package 1 Weight             | 2.5 kg  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|                       |                            |   |
|-----------------------|----------------------------|---|
| ✓                     | Reach Free Of Svhc         |   |
| ✓                     | Toxic Heavy Metal Free     |   |
| ✓                     | Mercury Free               |   |
| ✓                     | Rohs Exemption Information | Yes   |
|                       |                            |   |
| Reach Regulation      |                            | <a href="#">REACH Declaration</a>   |
|                       |                            |   |
| Eu Rohs Directive     |                            | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
|                       |                            |   |
| China Rohs Regulation |                            | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |