

Product data sheet

Specifications



Climasys forced vent. 170 m3/h, 230V without grille

NSYCVF170M230

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Range Compatibility	Prisma P
Flow Rate	Free flow rate: 170 m3/h at 50 Hz
Input Voltage	230 V 50/60 Hz

Complementary

Absorbed Power	17 W
Noise Level < At	41 dB
Height	External: 119 mm
Width	External: 119 mm
Depth	38 mm external:
Net Weight	0.82 kg
Material	Protective grille: steel
Device Composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 fixing collar

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	15 cm
Package 1 Length	17 cm
Package 1 Weight	846 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	20 cm
Package 2 Width	40 cm
Package 2 Length	30 cm
Package 2 Weight	8.954 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	PAM
Number Of Units In Package 3	320
Package 3 Height	75 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	300 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information