

Product data sheet

Specifications



Metal industrial cut-out box - high plain cover - H256xW206xD140 - IP55 - grey

NSYDA2520M

ⓘ Discontinued

Main

Range Of Product	Spacial SDB
Device Application	Multi-purpose
Product Or Component Type	Junction box
Enclosure Type	Empty enclosure
Type Of Front Cover	High plain cover
Colour	Light grey (RAL 7035)

Complementary

Enclosure Nominal Height	256 mm
Enclosure Nominal Width	206 mm
Enclosure Nominal Depth	140 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 1 cover screw
Cable Entry Number	5 diameter: 25.5 mm (M25) 5 diameter: 32.5 mm (M32) 5 diameter: 40.5 mm (M40) 5 diameter: 50.5 mm (M50)
Cover Fixing	Screw
Material	Steel
Surface Finish	Epoxy-polyester powder

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications