

# Product data sheet

Specifications



## Glazed door for Spacial S3D H1200xW800 RAL 7035, with lock

NSYDS3D128T

ⓘ Discontinued

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial S3D
Device Composition	1 door locking system
Quantity Per Set	Set of 1

### Complementary

Material	Door: sheet steel
Colour	Grey (RAL 7035)
Surface Finish	Textured epoxy polyester
Lock Type	Lock 3 mm double bar
Number Of Locks	1
Door Type	Glazed
Door Opening Side	Reversible (120 °)
Height	1200 mm nominal:
Width	800 mm nominal:
Net Weight	11.88 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	81 cm
Package 1 Length	122 cm
Package 1 Weight	13.856 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information