

Product data sheet

Specifications

Actassi - fixed slide - set of 2 - depth 600 mm



NSYGF356H5

Main

Range Of Product	Actassi
Product Or Component Type	Fixed slide
Accessory / Separate Part Category	Support accessory
Quantity Per Set	Set of 2

Complementary

Range Compatibility	Actassi VDS Actassi VDA
Material	Treated steel
Mounting Location	Upright
Depth	600 mm rack: 800 mm rack: 1000 mm rack:
Fixing Mode	By screws: upright
Permanent Permissible Load	60 kg
Distance Between Centers	258 mm
Distance Between Cable Supports	350 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	10.0 cm
Package 1 Length	44.0 cm
Package 1 Weight	944.0 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	400
Package 2 Height	45.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	390.6 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations