

NSYLAMCD

Fluorescent compact lamp, 11W, 220V 50/60Hz,
no socket + detector



Main

Range of product	Lighting and power sockets
Accessory / separate part category	Lighting accessory
Product or component type	Lamp
Device application	Multi-purpose
Device composition	Lamp Fixing elements Switch

Complementary

Outlet standard	Without socket
Rated lamp wattage	11 W
[Ue] rated operational voltage	220 V - 50/60 Hz
Bulb base	2G7
Bulb type	Fluorescent
Control type	Built-it switch
Luminous flux	900 lm
Service life in hours	8000 h
Electrical connection	Screw connector $\leq 2.5 \text{ mm}^2$
Mounting location	Top front of enclosure
Mounting support	DIN rail Upright Metal parts Cross rails
Fixing mode	Magnetic fixing Clip-in Screws
Range compatibility	Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SMX Spacial Spacial SFX Spacial Spacial SM

Spacial Spacial SF
Spacial Spacial S3D
Spacial Spacial CRN

Material	Plastic light grey
Height	40 mm
Width	372 mm
Depth	63 mm

Environment

IP degree of protection	IP20 conforming to IEC 60529
Electrical insulation class	Class II
Flame retardance	V0 conforming to UL 94
Electromagnetic compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4
Standards	UL 508 A
Product certifications	VDE
Ambient air temperature for operation	-16...65 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1004 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------