

# NSYLAMCF

Fluorescent compact lamp, 11W, 220V, 50/60Hz,  
socket UTE, type french



## Main

Range of product	Lighting and power sockets
Accessory / separate part category	Lighting accessory
Product or component type	Lamp
Device application	Multi-purpose
Device composition	Lamp Switch and power socket Fixing elements

## Complementary

Outlet standard	French
Rated lamp wattage	11 W
[Ue] rated operational voltage	230 V - 50/60 Hz
Bulb base	2G7
Bulb type	Fluorescent
Control type	Built-it switch
Luminous flux	900 lm
Service life in hours	8000 h
Electrical connection	Screw connector <= 2.5 mm <sup>2</sup>
Mounting location	Top front of enclosure
Mounting support	DIN rail Upright Cross rails Metal parts
Fixing mode	Magnetic fixing Clip-in Screws
Range compatibility	Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SMX Spacial Spacial SFX Spacial Spacial SM

Spacial Spacial SF  
Spacial Spacial S3D  
Spacial Spacial CRN

Material	Plastic light grey
Height	40 mm
Width	372 mm
Depth	63 mm

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Electrical insulation class	Class I
Flame retardance	V0 conforming to UL 94
Electromagnetic compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4
Standards	UL 508 A
Product certifications	VDE
Ambient air temperature for operation	-16...65 °C
Ambient air temperature for storage	-40...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------