


# Product data sheet

Specifications



## intermediate vertical upright - H800 - Cellean

NSYMTVUA80

### Main

Range Of Product	Cellean
Product Or Component Type	Vertical upright
Device Short Name	NSY
Accessory / Separate Part Category	Installation accessory
Product Compatibility	Floor-standing enclosure Wall-mounted enclosure
Sale Per Indivisible Quantity	6.0

### Complementary

Standards	EN/IEC 61439-1
Product Certifications	ASEFA
Height	800.0 mm
Net Weight	0.5 kg
Material	Galvanized steel

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	3.4 cm
Package 1 Length	78.5 cm
Package 1 Weight	513 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	6
Package 2 Height	3 cm
Package 2 Width	3 cm
Package 2 Length	79 cm
Package 2 Weight	3.078 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	18
Package 3 Height	35 cm
Package 3 Width	80 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	60 cm
Package 3 Weight	22.234 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---