



Main

Range	Actassi
Product name	Actassi OPB
Product or component type	19" enclosure
Device application	Cabling
Applications	To protect network connectivity equipment To mount 19" equipment To facilitate maintenance
Enclosure type	Open box
Front face	Glazed door
Colour	Light grey (RAL 7035)
Back face	Cut-out
Side face	Panel
Installation mode	Wall mounted

Complementary

Support equipment	1 x swing 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Door type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Front Rear Side
Removable parts	Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless Front door removable toolless
Device composition	3 x cable entries 1 x front glazed door 1 x open structure 2 x side panels 2 x front 19" uprights
Load rating	By unit : 3 kg

	Static : 25 kg
Number of cut-out	1 cut-out top 1 cut-out bottom 1 cut-out side
Material	Structure : sheet steel Door : sheet steel Upright : galvanized steel Door : sekurit glass
Surface finish	Epoxy-polyester powder
Product weight	17.8 kg
Enclosure nominal dimensions	- 380 mm 600 mm 400 mm
Number of rack unit	6U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------