

Product data sheet

Specifications



Spacial SF double ventilated door - 2200x800 mm

NSYPCV2D228

ⓘ Discontinued

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	19" door
Application	Electronic application
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial SF
Device Composition	1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 2 door 1 blocking system
Quantity Per Set	Set of 1

Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	Ventilated
Door Opening Side	Reversible (120 °)
Height	2200 mm nominal:
Width	800 mm nominal:

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations