



Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZT
Nominal height	1250 mm
Nominal width	500 mm
Nominal depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door 1 canopy 1 plinth

Complementary

Body type	Open top and bottom part assembled with side parts
Door type	Plain front
Number of doors	1 door(s)
Door opening side	Reversible (180 °)
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Top Front Bottom Rear
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	Veritas

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information