

Product data sheet

Specifications



Floor standing polyester enclosure,
Thalassa PLA, open bottom,
ventilated canopy,
1500x1250x420mm, IP44, IK10

NSYPLAZT15124G

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAZT
Nominal Height	1500 mm
Nominal Width	1250 mm
Nominal Depth	420 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body Type	Open top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (180 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Rear Top Bottom Front
Removable Parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-35...90 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	156.0 cm
Package 1 Width	128.0 cm
Package 1 Length	48.0 cm
Package 1 Weight	95.564 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	130 cm
Package 2 Width	100 cm
Package 2 Length	169 cm
Package 2 Weight	164 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations