



## Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZT
Nominal height	1500 mm
Nominal width	750 mm
Nominal depth	320 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 1 canopy 1 door 1 rear panel 1 plinth 2 side part

## Complementary

Body type	Open top and bottom part assembled with side parts
Door type	Plain front
Number of doors	1
Door opening side	Reversible 180 °
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Bottom Rear Front Top
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass

Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	Veritas

## Environment

IP degree of protection	IP44 with plinth type open bottom part and ventilated canopy IEC 60529
IK degree of protection	IK10 plain door IEC 62262
Fire resistance	960 °C IEC 62208
Ambient air temperature for storage	-35...90 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations