

Product data sheet

Specifications



PLD - Floor standing encl.polyester w/plinth open bottom 850x1115x320 IP43 DIN2

NSYPLD8122CG

 **Discontinued on:** Nov 23, 2020

 **Discontinued**

Main

Range	Thalassa
Category	Enclosure
Version	PLD
Enclosure Type	DIN enclosure Distribution enclosure
Nominal Height	850 mm
Nominal Width	1115 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Product Compatibility	Fuse 2

Complementary

Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 2 door 2 key lock 1 central upright
Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (180 °)
Lock Type	Key lock
Key Number	1242 E
Accessibility For Operation	Front Bottom
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP43 conforming to IEC 60529 (plinth type open bottom) IP54 conforming to IEC 60529 (with additional sealing kit)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-35...90 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	88 cm
Package 1 Width	34.5 cm
Package 1 Length	112 cm
Package 1 Weight	35 kg

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov