

# Product data sheet

Specifications



## PLD - Floor standing encl.polyester w/plinth open bottom 850x1115x320 IP43 DIN2

NSYPLD8122G

 **Discontinued on:** Jun 30, 2022

 **Discontinued**

### Main

Range	Thalassa
Category	Enclosure
Version	PLD
Enclosure Type	Distribution enclosure DIN enclosure
Nominal Height	850 mm
Nominal Width	1115 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Product Compatibility	Fuse 2

### Complementary

Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 2 door 1 key lock 1 left upright
Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (180 °)
Lock Type	Key lock
Key Number	1242 E
Accessibility For Operation	Bottom Front
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)

### Environment

Standards	IEC 62208
Ip Degree Of Protection	IP43 conforming to IEC 60529 (plinth type open bottom) IP54 conforming to IEC 60529 (with additional sealing kit)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK10 conforming to IEC 62262 (plain door)
<b>Fire Resistance</b>	960 °C conforming to IEC 62208
<b>Ambient Air Temperature For Storage</b>	-35...90 °C

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	88 cm
<b>Package 1 Width</b>	34.5 cm
<b>Package 1 Length</b>	112 cm
<b>Package 1 Weight</b>	35 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>