



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	1056 mm
Nominal width	852 mm
Nominal depth	350 mm
Enclosure mounting	Wall mounted
Device composition	Lock 1 Door 1 Body 1
Body type	One piece moulded with notches in the rear Built-in canopy
Door type	Transparent
Lock type	4 points lock, handle with 5 mm double bar insert

Complementary

Number of locks	1
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass body Tempered glass door
Colour	Grey RAL 7035
Standards	NEMA classification 4X NEMA classification 13 IEC 62208
Product certifications	UL

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK08 IEC 62262
Fire resistance	960 °C IEC 62208
Ambient air temperature for storage	-35...90 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations