



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	19" rack
Application	Electronic application
For enclosure nominal dimensions	W: 1800 mm
Rack type	Swing off-centred
Mounting location	On structure of enclosure
Range compatibility	Spacial SF Spacial SM
Device composition	Fixing elements 2 800 mm swing rack supports 1 hinged rack 1 side lid with handle
Quantity per set	Set of 1
Number of units 19"	36

Complementary

Material	Steel
Colour	Side plate : grey RAL 7035
Surface finish	Zinc coated
Lock type	Handle with ball lock
Fixing mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent permissible load	3.75 kg per unit with a maximum of 150 kg
Opening of the 19" racks	Reversible 120 °
Height	1800 mm
Width	800 mm
Depth	1701 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------