

Product data sheet

Specifications



HMI encl. Spacial S3CM.
H300xW400xD200IP54 IK10,
RAL7035.Rear door.

NSYS3CM304020

Main

Range	Spacial
Product Name	Spacial S3CM
Application	Human-machine dialogue application
Category	Control enclosure
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	400 mm
Enclosure Nominal Depth	200 mm
Installation Accessory Type	Suspension system
Product Destination	Interface
Device Composition	1 body 1 door with lock 2 rail 1 reinforcement plate 1 front trim frame

Complementary

Body Type	Single piece body
Door Type	Plain
Number Of Doors	Rear: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear
Removable Parts	Door by hinges Trim frame by screws 2 rails by screws
Material	Enclosure and front face: steel Trim frame: aluminium
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Front face: grey (RAL 7040)
Net Weight	9.146 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP54 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.0 cm
Package 1 Width	42.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	9.146 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations