



### Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	600 mm
Nominal width	400 mm
Nominal depth	200 mm
Product installation	Wall-mounting
Device composition	1 body 1 door 2 lock: door 2 perforated vertical profile drilled: door

### Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Lock: zamak Hinge: stainless steel Body and door: stainless steel 316L
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated

Thickness	1.5 mm
Net weight	9.52 kg

## Environment

Standards	IEC 62208
Product certifications	UL 508 type A CAN/CSA 22
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------