

# Product data sheet

Specifications



## Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 800x600x250mm, IP66

NSYS3X8625

### Main

|                      |                                                                                 |
|----------------------|---------------------------------------------------------------------------------|
| Range                | Spacial                                                                         |
| Product Name         | Spacial S3X                                                                     |
| Enclosure Type       | Multi-purpose                                                                   |
| Category             | Compact enclosure                                                               |
| Nominal Height       | 800 mm                                                                          |
| Nominal Width        | 600 mm                                                                          |
| Nominal Depth        | 250 mm                                                                          |
| Product Installation | Wall-mounting                                                                   |
| Device Composition   | 1 body<br>1 door<br>2 lock: door<br>2 perforated vertical profile drilled: door |

### Complementary

|                             |                                                                              |
|-----------------------------|------------------------------------------------------------------------------|
| Body Type                   | Single piece body, cross-shaped structure<br>Gutter shaped front rail        |
| Door Type                   | Plain                                                                        |
| Number Of Doors             | Front face: 1 door(s)                                                        |
| Door Opening Side           | Reversible (120 °)                                                           |
| Lock Type                   | 2 points lock, 3 mm double-bar                                               |
| Mounting Plate Description  | Without mounting plate                                                       |
| Type Of Gland Plate         | Without gland plate                                                          |
| Accessibility For Operation | Front                                                                        |
| Removable Parts             | Door by hinges                                                               |
| Material                    | Body and door: stainless steel 304L<br>Lock: zamak<br>Hinge: stainless steel |
| Surface Finish              | Body and door: Scotch-Brite® brushed<br>Lock: chromium plated                |
| Net Weight                  | 22.474 kg                                                                    |

### Environment

|                        |                             |
|------------------------|-----------------------------|
| Standards              | IEC 62208                   |
| Product Certifications | CAN/CSA 22<br>UL 508 type A |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                               |
|------------------------------|-------------------------------|
| Ip Degree Of Protection      | IP66 conforming to IEC 60529  |
| Ik Degree Of Protection      | IK10 conforming to IEC 62262  |
| Environmental Characteristic | Specific hygiene<br>Corrosive |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 81.99 cm |
| Package 1 Width              | 61.49 cm |
| Package 1 Length             | 27 cm    |
| Package 1 Weight             | 22.48 kg |
| Unit Type Of Package 2       | PAM      |
| Number Of Units In Package 2 | 12       |
| Package 2 Height             | 199 cm   |
| Package 2 Width              | 100 cm   |
| Package 2 Length             | 120 cm   |
| Package 2 Weight             | 296.5 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |                                                                                                                       |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                     |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)                                                            |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                         |
| Circularity Profile      | No need of specific recycling operations                                                                              |