



Main

Range	Spacial
Product name	Spacial SD
Enclosure type	Multi-purpose
Category	Monobloc control desk with rear panel
Nominal height	1000 mm
Nominal width	800 mm
Nominal depth	597 mm
Product installation	Floor-standing
Device composition	Door 1 Cable gland plate 1 Rear panel 1 Structure 1 Lock 2 door Adjustment rail 4 Pneumatic stay 2 desk lid Top plate 3 on top of control desk

Complementary

Body type	Single piece structure folded and welded
Door type	Plain
Number of doors	1 front
Door opening side	Reversible 120 ° door
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	1 entry plate
Accessibility for operation	Front Rear
Removable parts	Rear panel by screws Door by hinges Desk lid by hinges Cable gland plate by clipping screws

Blanking covers by screws

Material	Steel body
Surface finish	Epoxy-polyester powder
Thickness	1.5 mm

Environment

Standards	IEC 62208
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------