

Product data sheet

Specifications



Spacial SD Control desk with console & mounting plate - H1400xW1000xD1045 - IP55

NSYSDF1010P

! Discontinued

Main

Range	Spacial
Product Name	Spacial SD
Enclosure Type	Multi-purpose
Category	Control desk with console and desk
Nominal Height	1400 mm
Nominal Width	1000 mm
Nominal Depth	1045 mm
Product Installation	Floor-standing
Device Composition	1 structure 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid 1 front console door 1 desk lid 2 mechanical stay: front console door 6 lock: front door 1 handle lock: rear door 2 front door 2 rear door 1 mounting plate: lower part

Complementary

Body Type	Single piece structure folded and welded
Door Type	Plain
Number Of Doors	Front: 2 door(s) Rear: 2 door(s)
Door Opening Side	Reversible 120 ° front and rear doors Folding 75 ° desk lid and console cover
Lock Type	Handle lock, 5 mm double bar 2 points lock, 3 mm double-bar
Mounting Plate Description	Plain
Type Of Gland Plate	1 entry plate
Accessibility For Operation	Front Rear
Removable Parts	Desk lid by hinges Cable gland plate by clipping screws Mounting plate by mounting plate brackets Front door by hinges Front console door by hinges Rear door by hinges

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Body: steel
Surface Finish	Epoxy-polyester powder
Thickness	1.5 mm

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Contractual warranty

Warranty	18 months
----------	-----------