



Main

| | |
|------------------------------|--|
| Range | Spacial |
| Extended range | Spacial SFM |
| Application | Compartmentalised application |
| Product or component type | Suitable enclosure |
| Enclosure nominal height | 2000 mm |
| Enclosure nominal width | 800 mm |
| Enclosure nominal depth | 600 mm |
| Enclosure mounting | Floor-standing |
| Product specific application | Reduce the destructive effects of a short-circuit Insulating the control of a device |
| Device composition | 1 structure 1 rear panel 1 roof 2 intermediate crossbars 2 panels for modularity: top and bottom |

Complementary

| | |
|-----------------------------|--|
| Structure type | Vertical uprights joined with top and bottom frames Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Without gland plate |
| Accessibility for operation | Sides of enclosure Rear Front |
| Removable parts | Rear panel by screws Roof by screws |
| Material | Frame: galvanised steel Uprights: galvanised steel Panels: sheet steel |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|------------------------|
| | Hinge: zamak |
| Surface finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |

Environment

| | |
|-----------|-----------|
| Standards | IEC 62208 |
|-----------|-----------|

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|