

# Product data sheet

Specifications



## Spacial SF compartmentalised enclosure - assembled - 2000x800x800 mm

NSYSF20880M

### Main

Range	Spacial
Extended Range	Spacial SFM
Application	Compartmentalised application
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	800 mm
Enclosure Mounting	Floor-standing
Product Specific Application	Insulating the control of a device Reduce the destructive effects of a short-circuit
Device Composition	1 structure 1 rear panel 1 roof 2 intermediate crossbars 2 panels for modularity: top and bottom

### Complementary

Structure Type	Vertical uprights joined with top and bottom frames Perforated structure with a pitch of 25 mm Panels and doors built into the structure Formed from a single section
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear Sides of enclosure Front
Removable Parts	Rear panel by screws Roof by screws
Material	Frame: galvanised steel Uprights: galvanised steel Panels: sheet steel Hinge: zamak
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)

### Environment

Standards	IEC 62208
-----------	-----------

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	84.5 cm
Package 1 Width	89.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	85.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations