



## Main

Range	Spacial
Extended range	Spacial SF
Application	Prisma application
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	700 mm
Enclosure nominal depth	500 mm
Enclosure mounting	Floor-standing
Product specific application	Installing the Prisma Plus System P
Device composition	1 door 1 rear panel 1 roof 1 structure 1 locking system with handle for door 2 sliding rails 4 mounting plate bracket 4 adaptor upright

## Complementary

Structure type	Perforated structure with a pitch of 25 mm Panels and doors built into the structure Formed from a single section Vertical uprights joined with top and bottom frames
Door type	Glazed on front
Number of doors	1 on front
Door opening side	Reversible 120 °
Lock type	4 points lock, handle with 5 mm double bar insert on front door
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Rear Sides of enclosure

## Front

Removable parts	Rear panel fixed by screws Roof fixed by screws Door fixed by screws for hinge Mounting plate bracket fixed by screws Sliding rail fixed by screws Adaptor upright fixed by screws
Material	Galvanised steel for frame Galvanised steel for uprights Polyamide 6 with 30 % fibre glass for handle Securit glass for door Sheet steel for door Sheet steel for panels Zamak for hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure : grey RAL 7035 Handle : black RAL 9005

## Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1040 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------