



## Main

Range	Spacial
Product name	Spacial SFX
Enclosure type	Multi-purpose
Category	Suitable enclosure
Nominal height	1800 mm
Nominal width	800 mm
Nominal depth	400 mm
Product installation	Floor-standing
Device composition	1 cable gland plate 1 structure 4 mounting plate bracket 1 locking system with handle ( door ) 1 door with reinforcement frame

## Complementary

Body type	Single piece structure folded and welded Rear panel integrated
Door type	Plain
Number of doors	Front face : 1 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front Side
Removable parts	Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips
Material	Hinge : stainless steel Structure and door : stainless steel 304L

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	Handle : zamak
Surface finish	Enclosure : Scotch-Brite® brushed Handle : painted
Product weight	90 kg

## Environment

Standards	IEC 62208 NEMA 4X
Product certifications	UL
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------