



Main

| | |
|----------------------|---|
| Range | Spacial |
| Product name | Spacial SFX |
| Enclosure type | Multi-purpose |
| Category | Suitable enclosure |
| Nominal height | 2000 mm |
| Nominal width | 1200 mm |
| Nominal depth | 600 mm |
| Product installation | Floor-standing |
| Device composition | 1 structure 2 door with reinforcement frame 1 locking system with handle: door 4 mounting plate bracket 1 cable gland plate |

Complementary

| | |
|-----------------------------|--|
| Body type | Single piece structure folded and welded Rear panel integrated |
| Door type | Plain |
| Number of doors | Front face: 2 door(s) |
| Door opening side | Reversible (120 °) |
| Lock type | 3 points lock, handle with 5 mm double-bar insert |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Plain |
| Accessibility for operation | Front Side |
| Removable parts | Door by hinges Mounting plate bracket by screws Cable gland plate by clips |
| Material | Structure and door: stainless steel 304L Handle: zamak |

| | |
|----------------|---|
| | Hinge: stainless steel |
| Surface finish | Enclosure: Scotch-Brite® brushed Handle: painted |
| Net weight | 113.5 kg |

Environment

| | |
|------------------------------|-------------------------------|
| Standards | IEC 62208 |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Environmental characteristic | Corrosive Specific hygiene |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|