



Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 blocking system for left door 1 body 1 cable gland plate 1 locking system with handle for door 4 mounting plate bracket 2 door
Removable parts	Door fixed by screws for hinge Mounting plate bracket fixed by screws
Enclosure nominal height	1800 mm
Enclosure nominal width	1600 mm
Enclosure nominal depth	400 mm

Complementary

Number of doors	2 on front
Door opening side	Left 120 ° Right 120 °
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry
Material	Sheet steel for body Sheet steel for door

	Zamak for hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure : grey RAL 7035 Handle : black RAL 9005
Accessibility for operation	Front

Environment

Standards	IEC 62208
Product certifications	BV DNV UL
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------