

Product data sheet

Specifications



Spacial SM compact enclosure without mounting plate - 1800x800x500 mm

NSYSM18850

Main

Range	Spacial
Product Name	Spacial SM
Product Or Component Type	Compact enclosure
Application	Multi-purpose
Installation Accessory Type	Floor-standing
Device Composition	1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 door
Removable Parts	Door by screws hinge Mounting plate bracket by screws
Enclosure Nominal Height	1800 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	500 mm

Complementary

Number Of Doors	Front: 1 door(s)
Door Opening Side	Reversible (120 °)
Door Type	Plain
Lock Type	4 points lock, handle with 5 mm double bar insert
Body Type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Cable Entry	1 entry
Material	Body: sheet steel Door: sheet steel Hinge: zamak
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Accessibility For Operation	Front
Net Weight	96 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 62208
Product Certifications	DNV BV UL
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	193.0 cm
Package 1 Width	84.5 cm
Package 1 Length	59.0 cm
Package 1 Weight	96.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations