



Main

Range	Spacial
Product name	Spacial SMX
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	1800 mm
Nominal width	1200 mm
Nominal depth	400 mm
Product installation	Floor-standing
Device composition	1 body 1 cable gland plate 4 mounting plate bracket 2 door 1 locking system with handle (door)

Complementary

Body type	Single piece body folded and welded
Door type	Plain
Number of doors	Front face : 2 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front
Removable parts	Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips
Material	Hinge : stainless steel Body and door : stainless steel 316L Handle : zamak
Surface finish	Enclosure : Scotch-Brite® brushed

Handle : painted

Thickness	1.5 mm
Product weight	132 kg

Environment

Standards	IEC 62208
Product certifications	UL 508 CAN/CSA 22
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Specific hygiene Corrosive

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------