



Main

Range	Spacial
Product name	Spacial SMX
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	1800 mm
Nominal width	1600 mm
Nominal depth	400 mm
Product installation	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket

Complementary

Body type	Single piece body folded and welded
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	Reversible (120 °)
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Material	Body and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Surface finish	Enclosure: Scotch-Brite® brushed

	Handle: painted
Thickness	1.5 mm
Net weight	152 kg

Environment

Standards	IEC 62208
Product certifications	UL 508 CAN/CSA 22
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------