



## Main

|                      |  |
|----------------------|--|
| Range                | Spacial  |
| Product name         | Spacial SMX  |
| Enclosure type       | Multi-purpose  |
| Category             | Compact enclosure  |
| Nominal height       | 1800 mm  |
| Nominal width        | 800 mm   |
| Nominal depth        | 400 mm   |
| Product installation | Floor-standing   |
| Device composition   | 1 body<br>1 cable gland plate<br>1 door<br>4 mounting plate bracket<br>1 locking system with handle ( door ) |

## Complementary

|                             |  |
|-----------------------------|--|
| Body type                   | Single piece body folded and welded  |
| Door type                   | Plain  |
| Number of doors             | Front face : 1 door(s)   |
| Door opening side           | 120 °, reversible  |
| Lock type                   | 3 points lock, handle with 5 mm double-bar insert  |
| Mounting plate description  | Without mounting plate   |
| Type of gland plate         | Plain  |
| Accessibility for operation | Front  |
| Removable parts             | Door fixing: by hinges<br>Mounting plate bracket fixing: by screws<br>Cable gland plate fixing: by clips |
| Material                    | Hinge : stainless steel<br>Body and door : stainless steel 316L<br>Handle : zamak                        |
| Surface finish              | Enclosure : Scotch-Brite® brushed  |

|                |                  |
|----------------|------------------|
|                | Handle : painted |
| Thickness      | 1.5 mm           |
| Product weight | 98 kg            |

## Environment

|                              |                               |
|------------------------------|-------------------------------|
| Standards                    | IEC 62208                     |
| Product certifications       | UL 508<br>CAN/CSA 22          |
| IP degree of protection      | IP55 conforming to IEC 60529  |
| IK degree of protection      | IK10 conforming to IEC 62262  |
| Environmental characteristic | Specific hygiene<br>Corrosive |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 0940 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Need no specific recycling operations   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|