

# Product data sheet

Specifications



Spacial WM enclosure canopy  
W800xD400 Colour RAL7035.  
Fixings supplied.

NSYTJ8040

## Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial  |
| Accessory / Separate Part Category | Enclosure accessory                            |
| Product Or Component Type          | Canopy   |
| Application                        | Multi-purpose                                  |
| Range Compatibility                | Spacial Spacial CRN<br>Spacial Spacial S3D     |
| For Enclosure Nominal Dimensions   | -  |
| Mounting Location                  | On top of enclosure                            |
| Device Composition                 | canopy<br>fixing elements<br>instruction sheet |

## Complementary

|                   |                                   |
|-------------------|-----------------------------------|
| Material          | Galvanised steel                  |
| Colour            | Grey (RAL 7035)                   |
| Surface Finish    | Epoxy-polyester powder            |
| Fixing Mode       | By 4 screws - screw type M6       |
| Height            | 42 mm                             |
| Width             | 800 mm nominal:<br>809 mm real:   |
| Depth             | 400 mm nominal:<br>414.5 mm real: |
| Net Weight        | 5.2 kg                            |
| Mounting Diameter | 8 mm                              |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 4.000 cm  |
| Package 1 Width              | 43.000 cm |
| Package 1 Length             | 81.500 cm |
| Package 1 Weight             | 5.641 kg  |
| Unit Type Of Package 2       | PAM       |
| Number Of Units In Package 2 | 29        |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |            |
|------------------|------------|
| Package 2 Height | 90.000 cm  |
| Package 2 Width  | 100.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 176.589 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |