

Product data sheet

Specifications



Plug-in bridge, Linergy TR, 2 points,
for 35mm² terminal blocks, 2 way,
red, set of 10

NSYTRAL352

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block
Number Of Ways	2 ways

Complementary

Cable Cross Section	35 mm ²
Number Of Connections	2
Number Of Measurement Input	2 3 6 4 1
Quantity Per Set	Set of 10
Net Weight	19.4 g
Colour	Red

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	7.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	19.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	2.0 cm
Package 2 Width	7.0 cm
Package 2 Length	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	201.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	240
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.05 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations